iTHERM TS211

Messeinsatz zum Einbau in Thermometer

Insert for thermometer installation



Anwendungsbereich
• Universell einsetzbar
• Messbereich RTD: –200 … +600 °C (–328 … +1112 °F)
• Messbereich TC: –40 … +1100 °C (–40 … +2012 °F)
• Zum Einbau in Thermometer

Sensortypen Erstklassiger Sensor von Endress+Hauser für höchste Anlagenverfügbarkeit und Sicherheit:
• iTHERM StrongSens für erstklassige Vibrationsfestigkeit
• iTHERM QuickSens für weltweit kürzeste Ansprechzeiten
• Ein oder zwei drahtgewickelte Sensoren (WW)
• Ein oder zwei Dünnfilm-Sensoren (TF)

Application
• Universal range of application
• Measuring range RTD: –200 to +600 °C (–328 to +1112 °F)
• Measuring range TC: –40 to 1100 °C (–40 to 2012 °F)
• For installation in thermometers

Sensor types Best in class sensor from Endress+Hauser for highest plant availability and safety:
• iTHERM StrongSens for a best-in-class vibration resistance
• iTHERM QuickSens for the shortest response times worldwide
• Single or double wire wound sensor
• Single or double thin film sensor

Endress+Hauser
People for Process Automation