



FMA90 Housing

Image	*Name / Root*	*Description*
	DIN rail device FMA90 - ?? ? ? **A** ? ? ? ? ?	• Can be mounted on a standard 35 mm DIN rail in electrical cabinets • Comes with or without a display • Cover opens up to the left, underneath are the terminals • Comes with IP20

	Panel-mounted device
	FMA90 - ?? ? ? **B** ? ? ? ? ?
		• Can be mounted in 92 x 92 mm panel cutouts
		• Terminals are placed on the back of the device
		• If mounted in cabinet door, FMA90 comes with:
		  ◦ at front: IP65/NEMA Type 4
		  ◦ at rear: IP20

	Polycarbonate field housing FMA90 - ?? ? ? **C** ? ? ? ? ?	• Can be mounted on walls or on pipe mounting accessory with or without weather protection cover • Terminals are placed on the inside of the housing • Cable entries are placed on the bottom • Comes with IP65/NEMA Type 4x
	Aluminum field housing FMA90 - ?? ? ? **D** ? ? ? ? ?	• Aluminium housing that contains FMA90 mounted on DIN rail • Cable entries are placed on the bottom • Comes with IP65/NEMA Type 4x

Endress+Hauser
People for Process Automation