



## Table of content

<b>DK9013 Sensor set</b> .....	<b>3</b>
<b>DK9012 Sensor cable set</b> .....	<b>4</b>
<b>DK9014 Sensor holder set</b> .....	<b>5</b>
<b>DK9015 Installation set</b> .....	<b>6</b>
<b>DK9015 Installation set</b> .....	<b>7</b>
<b>DK9003 Conduit adapter set</b> .....	<b>8</b>
<b>DK9CM Coupling medium – coupling gel</b> .....	<b>9</b>
<b>DK9CM Coupling medium – coupling pad</b> .....	<b>10</b>
<b>71097625, Set test block – DN15-65</b> .....	<b>11</b>
<b>71528425, Set test block – DN50-4000</b> .....	<b>11</b>
<b>71612964, Set test block – DN50-600</b> .....	<b>12</b>

## DK9013 Sensor set

(For Prosonic Flow P 500)

Order code: DK9013 -\*\*  \*\*\*

060 Sensor version:

- **AA** C-030 (0,3 MHz)
- **AB** C-050 (0,5 MHz)
- **AC** C-100 (1 MHz)
- **AD** C-200 (2 MHz)



- **AE** C-500 (5 MHz)



- **AG** CH-050 (0,5 MHz)
- **AH** CH-100 (1 MHz)



## DK9012 Sensor cable set

(For Prosonic Flow P 500)

Order code: **DK9012** – \*\*\*\*\* PA\_\_

066 Cable:

- |             |                                   |                  |
|-------------|-----------------------------------|------------------|
| - <b>AA</b> | 5m/15ft, -40...80oC, -40...176oF  | TPE halogen free |
| - <b>AB</b> | 10m/30ft, -40...80oC, -40...176oF | TPE halogen free |
| - <b>AC</b> | 15m/35ft, -40...80oC, -40...176oF | TPE halogen free |
| - <b>AD</b> | 30m/60ft, -40...80oC, -40...176oF | TPE halogen free |



Order code: **DK9012** – \*\*\*\*\* PB\_\_

- |             |                                   |     |
|-------------|-----------------------------------|-----|
| - <b>AA</b> | 5m/15ft, -40...80oC, -40...176oF  | TPE |
| - <b>AB</b> | 10m/30ft, -40...80oC, -40...176oF | TPE |
| - <b>AC</b> | 15m/35ft, -40...80oC, -40...176oF | TPE |
| - <b>AD</b> | 30m/60ft, -40...80oC, -40...176oF | TPE |



Order code: **DK9012** – \*\*\*\*\* PA\_\_

- |             |                                    |      |
|-------------|------------------------------------|------|
| - <b>BA</b> | 5m/15ft, -50...170oC, -58...338oF  | PTFE |
| - <b>BB</b> | 10m/30ft, -50...170oC, -58...338oF | PTFE |
| - <b>BC</b> | 15m/35ft, -50...170oC, -58...338oF | PTFE |
| - <b>BD</b> | 30m/60ft, -50...170oC, -58...338oF | PTFE |



Order code: **DK9012** – \*\*\*\*\* PB\_\_

- |             |  |             |
|-------------|--|-------------|
| - <b>CA</b> | 5m/15ft, armored, -40...80oC, -40...176oF  | TPE armored |
| - <b>CB</b> | 10m/30ft, armored, -40...80oC, -40...176oF | TPE armored |
| - <b>CC</b> | 15m/35ft, armored, -40...80oC, -40...176oF | TPE armored |
| - <b>CD</b> | 30m/60ft, armored, -40...80oC, -40...176oF | TPE armored |



Order code: **DK9012** – \*\*\*\*\* PA\_\_

- |             |   |              |
|-------------|---|--------------|
| - <b>DA</b> | 5m/15ft, armored, -50...170oC, -58...338oF  | PTFE armored |
| - <b>DB</b> | 10m/30ft, armored, -50...170oC, -58...338oF | PTFE armored |
| - <b>DC</b> | 15m/35ft, armored, -50...170oC, -58...338oF | PTFE armored |
| - <b>DD</b> | 30m/60ft, armored, -50...170oC, -58...338oF | PTFE armored |



## DK9014 Sensor holder set

(For Prosonic Flow P 500 and W/I 400)

Order code: **DK9014** -  \*\*\*

010 Existing sensor version:

- **AA**<sup>1</sup> C-030 (0,3 MHz)
- **AB**<sup>1</sup> C-050 (0,5 MHz)
- **AC**<sup>1</sup> C-100 (1 MHz)
- **AD**<sup>1</sup> C-200 (2 MHz)



- **AE** C-500 (5 MHz)



- **AG** CH-050 (0,5 MHz)
- **AH** CH-100 (1 MHz)



---

<sup>1</sup> Same sensor holder type

## DK9015 Installation set

(For Prosonic Flow P 500 and W/I 400)

Order code: **DK9015** -  \*\*\*

010 Strapping band:

- **AA** DN15-DN32, 1/2"-1 1/4"



- **AB** DN32-DN65, 1 1/2"-2 1/2"



- **AC** DN50-DN150, 2"-6"

- **AD** DN150-DN200, 6"-8"

- **AE** DN200-DN600, 8"-24"



- **AF** DN600-DN2000, 24"-80"

- **AG** DN2000-DN4000, 80"-160"



- **BA** DN50-DN80, 2"-3"

- **BB** DN80-DN200, 3"-8"

- **BC** DN200-DN300, 8"-12"

- **BD** DN300-DN600, 12"-24"



## DK9015 Installation set

(For Prosonic Flow P 500 and W/I 400)

Order code: DK9015 -\*\*  \*\*

020 Mounting form:

- 1 Fastening, 1 traverse



- 2 Spacing ruler DN50-DN200 2"-8", W sensor



- 3 Spacing ruler DN200-DN600 8"-24", W sensor



- 4 Mounting rail DN50-DN200 2"-8", P sensor



- 5 Mounting rail DN200-DN600 8"-24", P sensor



- 6 Mounting rail, DN50-DN300, 2"-12",  
high temperature sensors



- 7 Mounting rail, DN300-DN600, 12"-24",  
high temperature sensors



## DK9003 Conduit adapter set

(For Prosonic Flow P 500 and W/I 400)

Order code: **DK9003** -\*\*  \*\*\*\*\*

010 Nominal diameter:

- **A** DN15-DN65, 1/2"-2 1/2"



- **B** DN50-DN4000, 2"-160"



Order code: **DK9003** -\*\*\*  \*\*\*

020 Cable entry:

- **B** Conduit adapter M20x1.5, cable glands

- **C** Conduit adapter NPT1/2", cable glands

- **D** Conduit adapter G1/2", cable glands



# DK9CM Coupling medium – coupling gel

(For Prosonic Flow P 500 and W/I 400)

Order code: **DK9CM** -

010 Version:

- 2 **Coupling medium**  
-40...170oC/-40...338oF, standard



- 3 **Adhesive coupling medium**  
-40...80oC/ -40...176oF
- 4 **Water soluble coupling medium**  
-20...80oC/ -4...176oF
- 6 **Coupling medium DDU19+DDU20**  
-20...60oC/ -4...140oF
- 7 **Coupling medium**  
-40...100oC/-40...212oF standard, type MBG2000



# DK9CM Coupling medium – coupling pad

(For Prosonic Flow P 500 and W/I 400)

Order code: **DK9CM** -

010 Version:

- **B**     **2x permanent coupling pad**  
           -40... 170oC/ -40... 338oF  
           0.3MHz, 0.5MHz, 1MHz, 2MHz
- **8**     **Pad, FPM**  
           0...170oC/32...338oF



- **D**     **1x permanent coupling pad**  
           -40... 170oC/ -40 ...338oF  
           5MHz



- **E**     **2x coupling foil**  
           150...220oC, 302...428oF     Tin
- **F**     **2x coupling foil**  
           210...370oC, 410...698oF     Zinc
- **G**     **2x coupling foil**  
           350...550oC, 662...1022oF    Aluminum



## 71097625, Set test block – DN15-65

(For Prosonic Flow P 500 and W/I 400)


Order code: 71097625



## 71528425, Set test block – DN50-4000

(For Prosonic Flow P 500 and W/I 400)

Order code: 71528425



## 71612964, Set test block – DN50-600

(For Prosonic Flow P 500 high temperature sensor)

Order code: 71612964

